
Subject: Re: z-Position of the Lumi Monitor

Posted by [Bernd Lewandowski](#) on Tue, 28 Jul 2009 12:23:23 GMT

[View Forum Message](#) <> [Reply to Message](#)

Hi Miriam,

after bringing together the actual numbers of the detectors in the forward spectrometer: The z-range of the Lumi detector is 10500mm to 12500mm.

At 10500mm the outer diameter of the beampipe is 110mm, same as at the z position of 12500mm.

So the parts to change the beampipe diameter for the Lumi detector are included in the 2m (z=10500mm - 12500mm).

Best Regards,
Bernd